



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD362410SS 36X24X10 N4X SS4 WM HC *Hoffman Enclosures, Inc.*

Catalog Number	CSD362410SS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount 1/4-Turn Latch Type 4X, 36X24X10, Brushed, Stainless 304
Weight per unit	57.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

Dimensions and Weight

Depth	10
Height	36
Size	36.00x24.00x10.00 in
Width	24

Descriptions

Description	36X24X10 N4X SS4 WM HC
extra long description	NVENT HOF CSD362410SS Wall Mount Ty
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Wallmount 1/4-Turn Latch Type 4X, 36x24x10, Brushed, Stainless 304
Product Type	Wall Mount Type 4X Enclosure

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510128722
Manufacturers Part Number	CSD362410SS
UPC	783510128722

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	57.7999

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant