



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD423612SSR 42X36X12 N4X SS4 HC (4)QTR TRN LTCH

Hoffman Enclosures, Inc.

Catalog Number	CSD423612SSR
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount Multi 1/4-Turn Latch 4X, 42X36X12, Brushed, SS304
Weight per unit	117.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

Dimensions and Weight

Depth	12
Height	42
Size	42.00x36.00x12.00 in
Width	36

Descriptions

Description	42X36X12 N4X SS4 HC (4)QTR TRN LTCH
extra long description	NVENT HOF CSD423612SSR 304SS CONCEP
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water, Concept enclosures house larger controls and feature streamlined styling with an attractive stroked finish, flush quarter-turn latches and an integral door ramp that ensures the door gasket sealing surface aligns with the enclosure body for secure closure.
Long Description	Concept Wallmount Multi 1/4-Turn Latch 4X, 42x36x12, Brushed, SS304
Product Type	304SS Concept 4X Addl Latches

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510148348
Manufacturers Part Number	CSD423612SSR
UPC	783510148348



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	117

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	12 Indoor, dust-resistant