



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor Connector Cable

CSMS5D5CY1602

UPC:782116056743

Dimensions:

- **Height:** 1 IN
- **Length:** 78.72 IN
- **Width:** 1IN

Warranties:

- 1 year

Specifications:

- **Type:** Accessory
- **Amperage Rating:** 8A
- **Connection:** Mini-style straight female
- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Environmental Rating:** NEMA 6P, IP68
- **Input Voltage:** 600V
- **Number Of Pins:** 5 pin
- **Number Of Wires:** 5-wire
white/red/green/orange/black
- **Operating Temperature:** -4° to 221°F (-20° to 105°C)
- **Power:** AC/DC
- **Series:** Global Plus
- **Switch Type:** Sensor connectivity
- **Wire Size:** #16 AWG

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - CSMS5D5CY1602](#)

Certifications: No Data

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor Connector Cable

CSMS5D5CY1602

UPC:782116056743

Dimensions:

- **Height:** 1 IN
- **Length:** 78.72 IN
- **Width:** 1IN

Warranties:

- 1 year

Specifications:

- **Type:** Accessory
- **Amperage Rating:** 8A
- **Connection:** Mini-style straight female
- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Environmental Rating:** NEMA 6P, IP68
- **Input Voltage:** 600V
- **Number Of Pins:** 5 pin
- **Number Of Wires:** 5-wire
white/red/green/orange/black
- **Operating Temperature:** -4° to 221°F (-20° to 105°C)
- **Power:** AC/DC
- **Series:** Global Plus
- **Switch Type:** Sensor connectivity
- **Wire Size:** #16 AWG

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - CSMS5D5CY1602](#)

Certifications: No Data

Product compliance: No Data



