



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CT24BK175L Cable Tie CT24BK175-L, 500/Case *Minnesota Mining (3M)*



Catalog Number	CT24BK175L
Manufacturer	Minnesota Mining (3M)
Description	Cable Tie, 183 MM;7.2 In Bundle Diameter, Black, 24 In;610 MM Length, Made In Usa, Nylon 6/6 Material, +185°F;+85°C Maximum Operating Temperature, -40°C;+32°F Minimum Operating Temperature, 50 BG Package Quantity, Uv Resistant;Weather Resistant Resistance Properties, Culus Listed;Rohs Compliant;UI Listed 181B-C;UI Listed Type 21/Type 21S;UI Standard 62275;UI. File # E116841, Self-Adhesive Style, 175 LB;79.379 KG;800 NM Tensile Strength, 0.09 In;2.3 MM Thickness, 0.03 LB (Each) Weight, 0.34 In;8.6 MM Width
Weight per unit	0.0026 (lbs/each)
Product Category	Cable Ties & Wraps

Descriptions

Description	CABLE TIE CT24BK175-L, 500/CASE
extra long description	3M 7000058851 3M™ Standard Nylon Ca
Special Features	Plenum Rated

Manufacturer Information

GTIN	00051128593189
Manufacturers Part Number	CT24BK175-L
UPC	051128593189

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Heavy Duty (175 lb)

Availability

minimum qty	50
-------------	----

Packaging

Carton	100
Package	500
Weight Per each	0.0026

Uses, Certifications, and Standards

Application	Heavy Duty
standard	UL Listed 62275 Type 21