



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## CT24NT175L Cable Tie CT24NT175-L, 500/Case *Minnesota Mining (3M)*

Catalog Number	CT24NT175L
Manufacturer	Minnesota Mining (3M)
Description	3M™ Standard Nylon Cable Ties Are Made With High-Quality Nylon 6/6 and Designed to Secure Wire Bundles and Harness Components Quickly, Without Slipping. The Curved Tip Allows For Faster Threading and Installation, and They Feature A Self-Locking Head.
Weight per unit	0.0025 (lbs/each)
Product Category	Cable Ties & Wraps

### Descriptions

Description	CABLE TIE CT24NT175-L, 500/CASE
extra long description	3M 7010400117 3M™ Standard Nylon Ca
Features	3M™ Standard Nylon Cable Ties are available in several tensile strengths ranging from 18 lb. to 175 lb. and multiple lengths ranging from 4 inches to 48 inches to cover your needs. They are offered in natural and red for indoor use and UV weather-resistant black for indoor and outdoor use. UL Listed 62275 Type 21 or 21S and Plenum Rated AH-2 for use in air handling spaces. Made in the USA.
Long Description	3M™ Standard Nylon Cable Ties are made with high-quality nylon 6/6 and designed to secure wire bundles and harness components quickly, without slipping. The curved tip allows for faster threading and installation, and they feature a self-locking head.
Product Type	3M™ Standard Nylon Cable Ties

### Manufacturer Information

Brand	3M
GTIN	00051128593196
Manufacturers Part Number	CT24NT175L
UPC	051128593196

### Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
----------------------	----------------------------

### Availability

minimum qty	50
-------------	----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Package	500
Weight Per each	0.0025