


3M™ Cable Tie Mounting Bases

3M™ Cable Tie Bases make mounting wire and cable a quick, easy and secure process. 2-way and 4-way configurations as well as adhesive-backed and screw mount options offer flexible mounting alternatives to meet a variety of applications.

RoHS 2011/65/EU Yes



	CTB2X1BGA-C	CTB1X1BGA-C	CTB75X75NTA-C	CTB75X75BKA-C
UPC	054007-06290	054007-06292	054007-06294	054007-06295
Material	ABS	ABS	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive (Screw Mount)	Foam Backed Adhesive	Foam Backed Adhesive
Color	Beige	Beige	Natural	Black (UV Resistant)
Length	2.0" (51 mm)	1.0" (25 mm)	0.74" (19 mm)	0.74" (19 mm)
Width	1.0" (25 mm)	1.2" (25 mm)	0.74" (19 mm)	0.74" (19 mm)
Height	0.35" (8,9 mm)	0.15" (3,8 mm)	0.22" (5,6 mm)	0.22" (5,6 mm)
Slot Width	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)
Slot Height	0.18" (4,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin				
	CTB1X1NTA-C	CTB1X1BKA-C	CTB60X41NTS-C	CTB87X62NTS-C
UPC	054007-06296	054007-06297	054007-95667	054007-95668
Material	Nylon	Nylon	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive	Screw Mount	Screw Mount
Color	Natural	Black (UV Resistant)	Natural	Natural
Length	0.99" (25 mm)	0.99" (25 mm)	0.60" (15 mm)	0.87" (22 mm)
Width	0.99" (25 mm)	0.99" (25 mm)	0.41" (10 mm)	0.62" (16 mm)
Height	0.22" (5,6 mm)	0.22" (5,6 mm)	0.28" (7,0 mm)	0.38" (10 mm)
Slot Width	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)	0.35" (8,9 mm)
Slot Height	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)	0.10" (2,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin			-	-