



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D26MBA D26 Relay Base Assembly With 120VAC Coil

*Eaton Corp*

Catalog Number	D26MBA
Manufacturer	Eaton Corp
Description	Eaton D26 Series Ac Relay Base Assembly, Four-Pole, 120V/60 HZ-110V Coil Voltage, 50 HZ, Blank Contact Configuration, 0 Blank Cavities
Weight per unit	1.9 (lbs/each)
Product Category	Nema Control Relays & Accy.

### Features

dimensions	4.0000 IN X 2.3800 IN X 3.5700 IN
Poles	4

### Descriptions

Description	D26 RELAY BASE ASSEMBLY WITH 120VAC COIL
extra long description	ETN D26MBA D26 Relay Base Assembly
Features	NEMA machine tool relays include the Freedom 600 V multi-pole (D15), fixed contact industrial control (BF, BFD), convertible contact industrial control (AR, ARD) and type M, multi-pole with convertible contacts (D26). These relays can be ordered as complete devices in any pole combination up to a maximum of 12NO or 8NC and 4NO poles. They are also designed for use on machines, process lines, conveyors and similar automatic and semiautomatic equipment.
Long Description	Eaton D26 Series AC Relay Base Assembly, Four-pole, 120V/60 Hz-110V coil voltage, 50 Hz, Blank contact configuration, 0 blank cavities
Product Type	D26 Relay Base Assembly With 120VAC Coil

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113181783
Manufacturers Part Number	D26MBA
UPC	782113181783

### Taxonomies, Classifications, and Categories

Category Description	600V MACHINE TOOL RELAYS
Type	Machine tool relay

### Packaging

Carton	1
Weight Per each	1.85



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL Listed Class NKCR2, CSA file No. LR353, UL Listed file E1230