



Powering Business Worldwide

pe.eaton.com

General Duty Cartridge Fuse Safety Switch

DG321NGB

UPC:782113120201

Dimensions:

- **Height:** 6 IN
- **Length:** 5.73 IN
- **Width:** 6.1 IN

Weight:5 LB

Notes:Maximum hp ratings apply only when dual element fuses are used

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG321NGB](#)

Certifications:

- UL Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

General Duty Cartridge Fuse Safety Switch

DG321NGB

UPC:782113120201

Dimensions:

- **Height:** 6 IN
- **Length:** 5.73 IN
- **Width:** 6.1 IN

Weight:5 LB

Notes:Maximum hp ratings apply only when dual element fuses are used

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG321NGB](#)

Certifications:

- UL Listed

Product compliance: No Data



