



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH322NRK 60A/3P HD Fusible Safety Switch W/Neut 240V Nema3r

Eaton Corp

Catalog Number	DH322NRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 60 A, Nema 3R, Painted Galvanized Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 3, 7.5/ 10, 15/ 10 HP (1, 3PH @STD/TD/250 VDC), #14-#2 Cu/Al
Weight per unit	20.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	60
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	16.5
Height	16.27
Width	9.5

Descriptions

Description	60A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA3R
extra long description	ETN DH322NRK 60A/3P HD FSBL Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 3, 7.5/ 10, 15/ 10 hp (1,3PH @Std/TD/250 Vdc), #14-#2 Cu/Al
Product Type	60A/3P HD FSBL Sfty SW W/Neut 240V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205830
Manufacturers Part Number	DH322NRK
UPC	782113205830

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	20

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed