



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH324NGK 200A/3P HD Fusible Safety Switch W/Neut 240V Nema1

Eaton Corp

Catalog Number	DH324NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 200 A, Nema 1, Painted Steel, Class H, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 15, 25/ 15, 60/ 40 HP (1, 3PH @STD/TD/250 VDC), #6-250 Kcmil Cu/Al
Weight per unit	43.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	200
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	240V

### Dimensions and Weight

Depth	30
Height	9.5
Width	18

### Descriptions

Description	200A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA1
extra long description	ETN DH324NGK 200A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 200 A, NEMA 1, Painted steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 15, 25/ 15, 60/ 40 hp (1,3PH @Std/TD/250 Vdc), #6-250 kcmil Cu/Al
Product Type	200A/3P HD FSBL Sfty SW W/Neut 240V N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206684
Manufacturers Part Number	DH324NGK
UPC	782113206684

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	43

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL Listed, NEC 230.62 (C) Compliant Barrier