



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH367FRK 800A/3P HD Fusible Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH367FRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 800 A, Nema 3R, Painted Galvanized Steel, Class L, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 500, 500 HP (3PH @480/600 V), (4)#1/0-(4)750 Kcmil Al
Weight per unit	163.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	800
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	57.5
Height	12.38
Width	27.5

Descriptions

Description	800A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH367FRK 800A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 800 A, NEMA 3R, Painted galvanized steel, Class L, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil Al
Product Type	800A/3P HD Fusible Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113589732
Manufacturers Part Number	DH367FRK
UPC	782113589732

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	163

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed