

Eaton DI06P-W

Catalog Number: DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386



General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI06P-W
UPC	Product Length/Depth
032664662386	2 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.001 lb	NOM cULus Listed

Product specifications

Frequency rating

60 Hz

Special features

Preset feature

Type

Dimmer

Voltage rating

120 V

Power consumption

600 W

Wiring method

Back and side

Environmental conditions

Indoor

Switch type

Single-pole, three-way

Load type

INC

MLV

HAL

Housing

Polycarbonate

Torque rating

14 lbf-inch

Material

Polycarbonate

Actuator

Slide

Color

White

Connection type

Wire lead

Resources

Brochures

Wiring Devices Buyer's Guide

Installation videos

How to install Eaton's universal slide dimmers

Specifications and datasheets

Eaton Specification Sheet - DI06P-W



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton DI06P-W

Catalog Number: DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386



General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI06P-W
UPC	Product Length/Depth
032664662386	2 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.001 lb	NOM
	cULus Listed

Product specifications

Frequency rating

60 Hz

Special features

Preset feature

Type

Dimmer

Voltage rating

120 V

Power consumption

600 W

Wiring method

Back and side

Environmental conditions

Indoor

Switch type

Single-pole, three-way

Load type

INC

MLV

HAL

Housing

Polycarbonate

Torque rating

14 lbf-inch

Material

Polycarbonate

Actuator

Slide

Color

White

Connection type

Wire lead

Resources

Brochures

Wiring Devices Buyer's Guide

Installation videos

How to install Eaton's universal slide dimmers

Specifications and datasheets

Eaton Specification Sheet - DI06P-W



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)