

# Eaton DI06P-W

Catalog Number: DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386



## General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI06P-W
UPC	Product Length/Depth
032664662386	2 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.001 lb	NOM
	cULus Listed

## Product specifications

### Frequency rating

60 Hz

### Special features

Preset feature

### Type

Dimmer

### Voltage rating

120 V

### Power consumption

600 W

### Wiring method

Back and side

### Environmental conditions

Indoor

### Switch type

Single-pole, three-way

### Load type

INC

MLV

HAL

### Housing

Polycarbonate

### Torque rating

14 lbf-inch

### Material

Polycarbonate

### Actuator

Slide

### Color

White

### Connection type

Wire lead

## Resources

### Brochures

Wiring Devices Buyer's Guide

### Installation videos

How to install Eaton's universal slide dimmers

### Specifications and datasheets

Eaton Specification Sheet - DI06P-W



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)