

# Eaton DI06P-W

Catalog Number: DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386



## General specifications

|                        |                      |
|------------------------|----------------------|
| Product Name           | Catalog Number       |
| Eaton decorator dimmer | DI06P-W              |
| UPC                    | Product Length/Depth |
| 032664662386           | 2 in                 |
| Product Height         | Product Width        |
| 4.25 in                | 2 in                 |
| Product Weight         | Certifications       |
| 0.001 lb               | NOM                  |
|                        | cULus Listed         |

## Product specifications

### Frequency rating

60 Hz

### Special features

Preset feature

### Type

Dimmer

### Voltage rating

120 V

### Power consumption

600 W

### Wiring method

Back and side

### Environmental conditions

Indoor

### Switch type

Single-pole, three-way

### Load type

INC

MLV

HAL

### Housing

Polycarbonate

### Torque rating

14 lbf-inch

### Material

Polycarbonate

### Actuator

Slide

### Color

White

### Connection type

Wire lead

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - DI06P-W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)