



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DI0D224V60W 24V 60W Omnidrive Dimmable Driver

Diode Led

Catalog Number	DI0D224V60W
Manufacturer	Diode Led
Description	24V 60W Omnidrive 2 Electronic Dimmable Driver
Weight per unit	2.3 (lbs/each)
Product Category	Lighting

### Features

Category	Specialty Items
----------	-----------------

### Material, Color, and Finish

Finish	BLACK GLOSS
Style	Transitional

### Descriptions

Description	24V 60W OMNIDRIVE DIMMABLE DRIVER
extra long description	ELECTRONIC DIMMABLE LED DRIVER, FANLESS TYPE; OMNIDRIVE[R] BRAND; ROHS COMPLIANT; CONNECTION TYPE SCREW TERMINAL; VOLTAGE RATING 24 VOLT DC (OUTPUT); CURRENT RATING 2.5 AMP (MAXIMUM LOAD), 0.75 AMP (FULL LOAD); POWER RATING 60 WATT; HOUSING TYPE BLACK POWDER COATED STEEL ENCLOSURE; TEMPERATURE RATING -40 TO 176 DEG F; RELATIVE HUMIDITY 20 TO 90 PERCENT NON-CONDENSING; APPLICATION INDOOR, DRY LOCATION; OVERALL DIMENSION 13.75 INCH LENGTH X 3 INCH WIDTH X 1.6 INCH HEIGHT; APPLICABLE STANDARD UL, CSA, ETL, FC
Long Description	24V 60W OMNIDRIVE 2 ELECTRONIC DIMMABLE DRIVER
Product Type	Electronic Dimmable Driver

### Manufacturer Information

Brand	Diode Led
GTIN	00848333011658
Manufacturers Part Number	DI-OD2-24V60W
UPC	848333011658

### Taxonomies, Classifications, and Categories

Type	Fixture Accents/Parts
------	-----------------------

### Packaging

Carton	1
Weight Per each	2.3