



Powering Business Worldwide

pe.eaton.com

Decorator Dimmer

DI10P-W

UPC:032664662447

Dimensions:

- **Height:** 4.38 IN
- **Length:** 2.06 IN
- **Width:** 3.13 IN

Warranties: No Data

Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection_Type:** Wire lead
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen, MLV
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 1000W

Supporting documents: No Data

Certifications:

- cULus Listed
- NOM

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Decorator Dimmer

DI10P-W

UPC:032664662447

Dimensions:

- **Height:** 4.38 IN
- **Length:** 2.06 IN
- **Width:** 3.13 IN

Warranties: No Data

Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection_Type:** Wire lead
- **Color:** White
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** Incandescent, halogen, MLV
- **Switch Type:** Single-pole, three-way
- **Material:** Polycarbonate
- **Wattage:** 1000W

Supporting documents: No Data

Certifications:

- cULus Listed
- NOM

Product compliance: No Data

