



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## DI120VSBRPD3024W Di-120V-Saber-PD30-24-WH

*Diode Led*

Catalog Number	DI120VSBRPD3024W
Manufacturer	Diode Led
Description	Under Cabinet Led Fixture, Under Cabinet Application, Dimmable, Powder Coated;White Finish, Dry Location;Indoor For Use In Environment, 0.96 In Height, 24 In Length, Aluminum (Housing) Material, Daisy-Chain Multiple Fixtures For Long Runs;Premium Diffusion:Eliminates Led Hot Spots Special Features, Cetlus Listed Standards Met, Fencer(R);Saber(TM) Sub Brand, 120 V Ac Voltage Rating, 5 Yr Warranty, 13 W Wattage, 3.62 In Width
Weight per unit	1.9 (lbs/each)
Product Category	Led Undercabinet Lighting

### Features

Category	Specialty Items
Safety Rating	ETL,UL
Voltage	120.00 LBS

### Material, Color, and Finish

Style	Transitional
-------	--------------

### Descriptions

Description	DI-120V-SABER-PD30-24-WH
-------------	--------------------------

### Manufacturer Information

Brand	Diode Led
GTIN	00848333011177
Manufacturers Part Number	DI-120V-SABER-PD30-24-WH-V2
UPC	848333011177

### Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

### Packaging

Carton	1
Weight Per each	1.9

### Uses, Certifications, and Standards

Energy Star	Yes Yes/No
-------------	------------