

DLS

4"



5 5/8"



TECHNICAL SPECIFICATIONS:

- :: Construction: Spun aluminum
- :: LED: Unique enclosed DOB (Driver On Board) LED board enclosed in clear plastic casing for better damp location performance
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: White translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working Voltage: 120V AC
- :: Dimmable
- :: LED: Seoul DOB (Driver On Board) Technology
- :: Power factor: 90% +
- :: Suitable for damp locations
- :: Maximum Ambient Temperature: 104°F
- :: Energy Star-rated
- :: Fit on recessed housings / Fit on standard 4" octagonal (40) or 3" octagonal (30) electrical boxes



ACCESSORIES INCLUDED



for DLS4



for DLS6

LED DISK LIGHTS—4" & 5" / 6" ROUND

CATALOG NO.	FINISH	WATTS	COLOR TEMP	LUMENS	DIAMETER
DLS4-27K	WHITE	9W	2700K	550~600LM	4"
DLS4-30K	WHITE	9W	3000K	550~600LM	
DLS4-41K	WHITE	9W	4000K	550~600LM	
DLS4-50K	WHITE	9W	5000K	550~600LM	
DLS6-27K	WHITE	15W	2700K	950~1000LM	5" / 6"
DLS6-30K	WHITE	15W	3000K	950~1000LM	
DLS6-41K	WHITE	15W	4000K	950~1000LM	
DLS6-50K	WHITE	15W	5000K	950~1000LM	
DLS6-30K-BR	BRONZE	15W	3000K	950~1000LM	
DLS6-30K-BN	BRUSHED NICKEL	15W	3000K	950~1000LM	



DLS

4"



5 5/8"



TECHNICAL SPECIFICATIONS:

- ⌘ Construction: Spun aluminum
- ⌘ LED: Unique enclosed DOB (Driver On Board) LED board enclosed in clear plastic casing for better damp location performance
- ⌘ Gasket: close cell Neoprene foam gasket
- ⌘ Lens: White translucent acrylic
- ⌘ Isolated driver for improved thermal management
- ⌘ CRI: 90
- ⌘ Working Voltage: 120V AC
- ⌘ Dimmable
- ⌘ LED: Seoul DOB (Driver On Board) Technology
- ⌘ Power factor: 90% +
- ⌘ Suitable for damp locations
- ⌘ Maximum Ambient Temperature: 104°F
- ⌘ Energy Star-rated
- ⌘ Fit on recessed housings / Fit on standard 4" octagonal (40) or 3" octagonal (30) electrical boxes



ACCESSORIES INCLUDED



for DLS4



for DLS6

LED DISK LIGHTS—4" & 5" / 6" ROUND

CATALOG NO.	FINISH	WATTS	COLOR TEMP	LUMENS	DIAMETER
DLS4-27K	WHITE	9W	2700K	550~600LM	4"
DLS4-30K	WHITE	9W	3000K	550~600LM	
DLS4-41K	WHITE	9W	4000K	550~600LM	
DLS4-50K	WHITE	9W	5000K	550~600LM	
DLS6-27K	WHITE	15W	2700K	950~1000LM	5" / 6"
DLS6-30K	WHITE	15W	3000K	950~1000LM	
DLS6-41K	WHITE	15W	4000K	950~1000LM	
DLS6-50K	WHITE	15W	5000K	950~1000LM	
DLS6-30K-BR	BRONZE	15W	3000K	950~1000LM	
DLS6-30K-BN	BRUSHED NICKEL	15W	3000K	950~1000LM	

