

7.1

Air Conditioning Disconnects

Fused, Unfused and Molded Case Switch

DPU222R12W



ACD with Factory-Installed Whip—Non-Fused Pullout ①

| Whip Diameter | Hot Wire Size | Ground Wire Size | Flexible Conduit Length | Non-Metallic Fittings | Catalog Number |
|---------------|---------------|------------------|-------------------------|-----------------------|----------------|
| 1/2 Inch | #10 | #10 | 6 ft (1.8m) | 1–90°, 1—Straight | DPU222R12W |
| 3/4 Inch | #8 | #10 | 6 ft (1.8m) | 1–90°, 1—Straight | DPU222R34W |

DPU362R



Three-Phase Non-Fused ACD

| Main Ampere Rating | Maximum hp Rating | | Wire Size Range Cu/Al 60°C or 75°C | Catalog Number |
|--------------------|-------------------|------|---------------------------------------|----------------|
| | 120V | 240V | | |
| 60 | 10 | 15 | #14–3 | DPU362R |

7

Cross-Reference

Cross-Reference

| Description | Catalog Number | | | | | |
|--|-----------------|-----------|-----------|-----------------------|-------------|----------|
| | Eaton | Square D® | GE® | Siemens® (Murray®) | Milbank | Midwest |
| Metallic/Galvanized Steel Enclosure | | | | | | |
| 30A fused | DPF221R | — | TF30R | WF2030 | U3830 | U035F2 |
| 60A fused | DPF222R | — | TF60R | WF2060 | U3860 | U065F1 |
| 60A non-fused | DPU222R | — | TFN60R | — | U3800 | U065P010 |
| 60A non-fused compact design | DPU222R | — | — | WNFC2060 | — | — |
| 60A molded case switch | DPB222R | QO200TR | TNA60R1 | WNAS2060 | — | U065NA1 |
| 60A non-fused with ground fault receptacle | DPU222RGF | — | TFN60RGFR | WN2060GFCI | U3822-20GR | U065P010 |
| 30A fused with ground fault receptacle | DPF221RGF | — | — | WF2030GFCI | — | U035F010 |
| 60A fused with ground fault receptacle | DPF222RGF | — | — | WF2060GFCI | — | U065F010 |
| 60A non-fused with 1/2-inch wire harness | DPU222R12W | — | — | — | — | — |
| 60A non-fused with 3/4-inch wire harness | DPU222R34W | — | — | — | — | — |
| 60A three-phase 600V molded case switch | DPU362R | — | — | — | — | U0653F |
| Non-Metallic/Polycarbonate Enclosure | | | | | | |
| 30A fused | ACD221RNM-A2 | — | TPF30R | WF2030PL | — | P035F |
| 60A fused | ACD222RNM-A2 | — | TPF60R | WF2060PL | — | P065F |
| 60A non-fused | ACD222URNM-A2 | — | TPN60R1 | WN2060PL | — | P065P1 |
| 60A molded case switch | B60NARNM-A2 | QO200TRNM | TPNA60R1 | WNAS2060PL | — | P065NA1 |
| 30A fused with 15A ground fault receptacle | DPF221RGF15WRTR | — | — | — | — | — |
| 30A fused with 20A ground fault receptacle | DPF221RGF20WRTR | — | — | — | — | — |
| 60A fused with 15A ground fault receptacle | DPF222RGF15WRTR | — | — | — | — | — |
| 60A fused with 20A ground fault receptacle | DPF222RGF20WRTR | — | — | — | — | — |
| 60A non-fused with 15A ground fault receptacle | DPU222RGF15WRTR | — | — | — | — | — |
| 60A non-fused with 20A ground fault receptacle | DPU222RGF20WRTR | — | — | — | U3822-20GWR | — |

Note

① Eaton Quick ProSM designated item.