



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DT305 Dual Tech Occ Sensor 24VDC Center Mount 360 40 KHZ Wattstopper

Catalog Number	DT305
Manufacturer	Wattstopper
Description	This Dual Technology Ceiling Sensor Combines The Benefits Of Passive Infrared (Pir) and Ultrasonic Technologies to Detect Occupancy. Sensors Have A Flat, Unobtrusive Appearance and Provide 360 Degrees Of Coverage. Up to 1000 SQ Feet.
Weight per unit	0.3600 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
Connection Type	Wired
included	Sensor Mask
indicator	LED Light
Input Voltage	18 to 28 VDC/VAC
Mounting Type	Ceiling Tile, 4 in Octagonal J-Box, Surface
Number of Connections	1.0
Sensor Type	Occupancy
supply voltage	24 VDC/VAC
Voltage	24.0 V

Descriptions

Description	DUAL TECH OCC SENSOR 24VDC CENTER MOUNT 360 40 KHZ
extra long description	WATT DT-305 Dual Tech Occupancy Se
Features	Light Level Sensor, Adjustable Time Delay, Indicator Lights, Power Pack Required, Sensitivity Adjustment
Long Description	This Dual technology Ceiling Sensor combines the benefits of passive infrared (PIR) and ultrasonic technologies to detect occupancy. Sensors have a flat, unobtrusive appearance and provide 360 degrees of coverage. Up to 1000 sq feet.
Product Type	Dualtech OCCSEN24VDC CTR MNT 360° 40KHZ
Special Features	Dual Technology

Manufacturer Information

Brand	Legrand-Wattstopper
GTIN	00754182913831
Manufacturers Part Number	DT305
UPC	754182913831

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SENSOR



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 35.0

Packaging

Carton 1

Weight Per each 0.36

Uses, Certifications, and Standards

Application Classrooms, Open Office, Large Offices, Computer Rooms

nema rating WD 7-2000

standard ROHS, WELL, DLC, PEP, IOXT, UL, cUL