



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DT305 Dual Tech Occ Sensor 24VDC Center Mount 360 40 KHZ *Wattstopper*

Catalog Number	DT305
Manufacturer	Wattstopper
Description	Combines The Benefits Of Passive Infrared (Pir) and Ultrasonic Technologies to Detect Occupancy.
Weight per unit	0.3600 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
Connection Type	Wired
included	Sensor Mask
indicator	LED Light
indoor/outdoor	Indoor
Input Voltage	18 to 28 VDC/VAC
Mounting Type	Ceiling Tile, 4 in Octagonal J-Box, Surface
Number of Connections	1.0
sensing range	1000 sq ft
Sensor Type	Occupancy
supply voltage	24 VDC/VAC
Switch Type	Motion Sensor
Voltage	24.0 V
Wire Size	#14 - #10 Awg

Descriptions

Description	DUAL TECH OCC SENSOR 24VDC CENTER MOUNT 360 40 KHZ
extra long description	P&S DT305 DT OCC SNSR24VDC, CNTRMN
Features	Motion Sensor
Long Description	Combines the benefits of passive infrared (PIR) and ultrasonic technologies to detect occupancy.
Product Type	DT Occ SNSR24VDC, CNTRMNT 360, 40 KHZ
Special Features	Dual Technology

Manufacturer Information

Brand	Legrand-Wattstopper
GTIN	00754182913831
Manufacturers Part Number	DT305
UPC	754182913831

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SWITCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 35.0

Packaging

Carton 1

Weight Per each 0.36

Uses, Certifications, and Standards

Application Classrooms, Open Office, Large Offices, Computer Rooms

nema rating WD 7-2000

standard ROHS, UL, cUL