



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVRP253PLA Diva 250W Led/Elv 3WAY Light Almond Lutron

Catalog Number	DVRP253PLA
Manufacturer	Lutron
Description	Diva Reverse-Phase Dimmer - Gloss Finish, CFL/Led (Screw-Based), Incandescent/Halogen, Electronic Low-Voltage, 3-Way/Single-Pole, 250W CFL/Led or 500W Inc/Hal/Elv In Light Almond
Weight per unit	0.2700 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Switch Type	Paddle Switch
Voltage Rating	120
Wattage	250/500

Material, Color, and Finish

Color	Light Almond
-------	--------------

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	DIVA 250W LED/ELV 3WAY LIGHT ALMOND
extra long description	LUT DVRP-253P-LA DIVA 250W LED 500W
Long Description	Diva Reverse-phase Dimmer - Gloss Finish, CFL/LED (Screw-based), Incandescent/Halogen, Electronic Low-voltage, 3-way/single-pole, 250W CFL/LED or 500W inc/hal/ELV in light almond
Product Type	Diva 250W Led 500W Elv In Light Almond
Special Features	Controls 120 V/250 W LED/CFL, and 500 W Inc and ELV loads. Paddle turns on/off. Slide up to brighten, down to dim.

Manufacturer Information

Brand	Lutron
GTIN	00784276221689
Manufacturers Part Number	DVRP-253P-LA
UPC	784276221689



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Dimmer, reverse-phase, 3-way/single-pole

Packaging

Carton 1

Weight Per each 0.27

Uses, Certifications, and Standards

Application Lighting Control

Enclosure Plastic

environmental conditions Indoor use only

Mounting WALLBOX

Operating Temperature 32 to 104

standard UL, CSA, NOM