

Search

[Advanced Search](#)[Product Site Map](#) [Go](#)

January 28, 2004

You Are Here: [Product Catalog](#) > [Drills](#) > [Hammerdrills](#)**Heavy-Duty XRP™ 1/2" (13mm) 14.4V Cordless Hammerdrill/Drill/Driver Kit - DW984K-2**[Email this tool to a friend](#)[Printer-friendly version](#)[Click To Enlarge Photo](#)**Features:**

- DEWALT Built Series 4000 high torque motor provides 400 in-lbs of maximum torque
- Exclusive 3-speed all metal transmission features a MAX 3rd Speed at 1,800 rpm which is 29% faster than high speed
- Hammerdrill mode: 30,600 bpm in MAX 3rd speed drills faster holes in masonry
- 1/2" ratcheting chuck lock with carbide jaws prevents bits from slipping
- Extended run-time batteries provide more work per charge and maximum number of recharges with NO MEMORY
- Superior ergonomics and balance provide increased comfort and control

[Warranty Information](#)**SPECIFICATIONS**

Voltage	14.4 V
Keyless Chuck	Yes
Automatic Spindle Lock	Yes
Adjustable Clutch	Yes
Chuck Size	1/2" "
Max. Torque	400 in-lbs
No Load Speed	0-450/0-1,400/0-1,800 rpm
Blows/Min	0-30,600 in MAX 3rd Speed bpm
Capacity In Steel	1/2" "
Capacity In Wood	1-3/4" "
Capacity In Concrete	1/4" "
Tool Weight	5.25 lbs
Shipping Weight	12 lbs

Includes:

- 1 hour charger
- (2) 14.4V XR PACK® batteries
- double-ended screwdriver bit
- heavy-duty kit box

[360° Click Here To See The Product Virtual Tour](#)[See more detailed photos on this product](#)**Featured Online Retailers****Toolsforless**

INTERNATIONAL TOOL CORPORATION

MAX Tool[Full List of Authorized DEWALT Online Retailers](#)**Find a Retailer Near You**

Zip/Postal Code: Country:

Related Accessories**Concrete & Masonry Drilling**[More Details](#)**Related Tools****DW988K-2**

Heavy-Duty XRP™ 1/2" (13mm) 18V Cordless Hammerdrill/Drill/Driver Kit

[More Details](#)**DW911**

Heavy-Duty Worksite Radio/Charger

[More Details](#)**DW983KS-2**

Heavy-Duty XRP™ 14.4V Cordless Drill/Driver/Trim Saw Combo Kit

[More Details](#)

Search

[Advanced Search](#)[Product Site Map](#) **Go**

January 28, 2004

You Are Here: [Product Catalog](#) > [Drills](#) > [Hammerdrills](#)**Heavy-Duty XRP™ 1/2" (13mm) 14.4V Cordless Hammerdrill/Drill/Driver Kit - DW984K-2**[Email this tool to a friend](#)[Printer-friendly version](#)[Click To Enlarge Photo](#)**Features:**

- DEWALT Built Series 4000 high torque motor provides 400 in-lbs of maximum torque
- Exclusive 3-speed all metal transmission features a MAX 3rd Speed at 1,800 rpm which is 29% faster than high speed
- Hammerdrill mode: 30,600 bpm in MAX 3rd speed drills faster holes in masonry
- 1/2" ratcheting chuck lock with carbide jaws prevents bits from slipping
- Extended run-time batteries provide more work per charge and maximum number of recharges with NO MEMORY
- Superior ergonomics and balance provide increased comfort and control

[Warranty Information](#)**SPECIFICATIONS**

Voltage	14.4 V
Keyless Chuck	Yes
Automatic Spindle Lock	Yes
Adjustable Clutch	Yes
Chuck Size	1/2" "
Max. Torque	400 in-lbs
No Load Speed	0-450/0-1,400/0-1,800 rpm
Blows/Min	0-30,600 in MAX 3rd Speed bpm
Capacity In Steel	1/2" "
Capacity In Wood	1-3/4" "
Capacity In Concrete	1/4" "
Tool Weight	5.25 lbs
Shipping Weight	12 lbs

Includes:

- 1 hour charger
- (2) 14.4V XR PACK® batteries
- double-ended screwdriver bit
- heavy-duty kit box

[360° Click Here To See The Product Virtual Tour](#)[See more detailed photos on this product](#)**Featured Online Retailers****Toolsforless**

INTERNATIONAL TOOL CORPORATION

MAX Tool[Full List of Authorized DEWALT Online Retailers](#)**Find a Retailer Near You**

Zip/Postal Code: Country:

Related Accessories**Concrete & Masonry Drilling**[More Details](#)**Related Tools****DW988K-2**

Heavy-Duty XRP™ 1/2" (13mm) 18V Cordless Hammerdrill/Drill/Driver Kit

[More Details](#)**DW911**

Heavy-Duty Worksite Radio/Charger

[More Details](#)**DW983KS-2**

Heavy-Duty XRP™ 14.4V Cordless Drill/Driver/Trim Saw Combo Kit

[More Details](#)