



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DWZ100B Multivolt 365 Day Astro Supercap 1 Channel 20A SP

Nsi Industries

Catalog Number	DWZ100B
Manufacturer	Nsi Industries
Description	The Tork DMZ100B 365/7-Day Astronomic Digital Timer Is Designed For 120-277 Volt Loads and Has A Noryl Plastic Enclosure With A Locking Hasp For Outdoor Use. Automate Your Home or Office to Save Energy and Money Using The Intuitive Programming Interface and Light Sensitive Activation to Activate Lights or Signage When The Ambient Light Level Drops Below A Customizable Threshold. Features One SPDT Output Channel With Automatic Voltage Detection and Automatic Daylight Saving Adjustment. Designed For Commerci
Weight per unit	2.2 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-208-240-277
Phase	Single Phase
Poles	1
Timing Range	365 Day-7 Day Advanced

Dimensions and Weight

Size	L=5.000 - H=9.125 - W=4.500
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MULTIVOLT 365 DAY ASTRO SUPERCAP 1 CHANNEL 20A SP
extra long description	TORK DWZ100B 356 Day Astro Digital
Features	Digital timers simplify your life by automating repeating parts of your schedule, saving the user time, energy and money. The DWZ100B is a 365/7-day astronomic lighting control timer, ideal for applications in the home, office, factory, church or school. Use a photocell sensor to detect when the ambient light level drops below a programmable threshold, then turn on everything from signage to meeting room lights. Program in up to 99 different on/off settings with unique schedules for each day of the week us
Long Description	The TORK DMZ100B 365/7-Day Astronomic Digital Timer is designed for 120-277 volt loads and has a Noryl plastic enclosure with a locking hasp for outdoor use. Automate your home or office to save energy and money using the intuitive programming interface and light sensitive activation to activate lights or signage when the ambient light level drops below a customizable threshold. Features one SPDT output channel with automatic voltage detection and automatic daylight saving adjustment. Designed for commerci
Product Type	356 Day Astro Digital Timer 1CH Title 24
Special Features	99 On-Off Set Points - Astronomic Time Switch With Holiday Schedule And Manual Override

Manufacturer Information

Brand	NSi
GTIN	00786261821898
Manufacturers Part Number	DWZ100B
UPC	786261821898

Taxonomies, Classifications, and Categories

Category Description	1PH MANUAL STARTERS
Type	365 Day-7 Day Advanced - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	2.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Noryl Indoor-Outdoor
environmental conditions	-40 to + 158 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 158 F
standard	UL917