



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50KL552 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL552
Manufacturer	Eaton Corp
Description	Limit Switch Operator, E50, Accessory, Standard Ball Bearing Roller, 1.1 In-Oz Min. Return, Used With Side Rotary
Weight per unit	0.0500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

### Features

dimensions	2.7200 IN X 0.6900 IN X 0.6100 IN
------------	-----------------------------------

### Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL552 E50 OPERATING LEVER
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	Limit Switch Operator, E50, Accessory, Standard ball bearing roller, 1.1 in-oz min. return, Used with side rotary
Product Type	E50 Operating Lever
Special Features	Used with Used with side rotary

### Manufacturer Information

Brand	Eaton
GTIN	00782113322186
Manufacturers Part Number	E50KL552
UPC	782113322186

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory

### Packaging

Carton	1
Weight Per each	0.05



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Industrial Facilities/Factories - Other .....
Operating Temperature .....	10 .....
standard .....	UL Listed, CSA Certified, CE, RoHS Compliant .....