



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57MAL18A2EB1

UPC:782113384627

Dimensions:

- **Height:** .71 IN
- **Length:** 3.39 IN
- **Width:** .71 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Connection:** Mini
- **Contact Rating:** 250 mA at 250V
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC, NO
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 122°F
- **Series:** E57

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57MAL18A2EB1](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57MAL18A2EB1

UPC:782113384627

Dimensions:

- **Height:** .71 IN
- **Length:** 3.39 IN
- **Width:** .71 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Connection:** Mini
- **Contact Rating:** 250 mA at 250V
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC, NO
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 122°F
- **Series:** E57

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57MAL18A2EB1](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



