






Carlton




1/2"



3/4"



1"



| PART NO. | CONDUIT SIZE | VOLUME CU. IN. (ML) | DIM. A | DIM. B |
|--|--------------|---------------------|-------------|-------------|
| E982DFN E982DFN-CTN E982DFNL E982DFNL-4 | 1/2" [16] | 18 [295] | 1.53 [38.9] | .568 [14.4] |
| E982EFN E982EFN-CTN E982EFNL E982EFNL-4 | 3/4" [21] | 18 [295] | 1.20 [30.6] | .672 [17.1] |
| E982FFN E982FFN-CTN | 1" [27] | 18 [295] | 1.47 [44.2] | .805 [20.4] |

GENERAL NOTES

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

C SEE ERN 2015298 FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: 5AM000012

Thomas & Betts
www.tnb.com

DESCRIPTION: **FS BOXES - 1/2", 3/4" & 1" TWO PORTS ONE SIDE (1" SIZE SHOWN)**

ORIGINAL PROJECT NO / (ERN NO)
/ ()


SHEET NO:
1 OF 1

REV. NO:
C


DRAWING NO:
WSD-AC02250




Carlton




1/2"



3/4"



1"



| PART NO. | CONDUIT SIZE | VOLUME CU. IN. (ML) | DIM. A | DIM. B |
|--|--------------|---------------------|-------------|-------------|
| E982DFN E982DFN-CTN E982DFNL E982DFNL-4 | 1/2" [16] | 18 [295] | 1.53 [38.9] | .568 [14.4] |
| E982EFN E982EFN-CTN E982EFNL E982EFNL-4 | 3/4" [21] | 18 [295] | 1.20 [30.6] | .672 [17.1] |
| E982FFN E982FFN-CTN | 1" [27] | 18 [295] | 1.47 [44.2] | .805 [20.4] |

GENERAL NOTES

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

C SEE ERN 2015298 FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: 5AM000012

Thomas & Betts
www.tnb.com

DESCRIPTION: **FS BOXES - 1/2", 3/4" & 1" TWO PORTS ONE SIDE (1" SIZE SHOWN)**

ORIGINAL PROJECT NO / (ERN NO)
/ ()

SHEET NO:
1 OF 1

REV. NO:
C

DRAWING NO:
WSD-AC02250