



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EAJX26SA 3/4" Cond Body & CVR, Alu *Crouse-Hinds*

Catalog Number	EAJX26SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Eaj Conduit Outlet Box With Cover, 3-3/16" Cover Opening Diameter, Copper-Free Aluminum, X Shape, 3/4"
Weight per unit	2.2 (lbs/each)
Product Category	Alum

Features

Cable Entry	(4) Side
dimensions	5.5600 IN X 2.7800 IN X 5.5600 IN
Material	Copper-Free Aluminum

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	3/4" COND BODY & CVR, ALU
extra long description	CRS-H EAJX26 SA 3/4 NPT X AL ROUND
Features	Crouse-Hinds series EAB and EAJ explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes.EAB and EAJ outlet boxes are manufactured in five different hub configurations with mounting feet and 16 pitch cover threads.
Long Description	Eaton Crouse-Hinds series Condulet EAJ conduit outlet box with cover, 3-3/16" cover opening diameter, Copper-free aluminum, X shape, 3/4"
Product Type	3/4 NPT X Al Round Base 3 3/16 CVR
Special Features	With Cover, Cover Opening Diameter 3-3/16 In

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274943633
Manufacturers Part Number	EAJX26 SA
UPC	782274943633

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2