

# NEER Aluminum Entrance Caps

## ECO: Clamp-on Aluminum Entrance Caps

### Applications

- Clamp type aluminum entrance caps for threaded or unthreaded rigid conduit, IMC or EMT service masts.

### Standard Material/Finish


- ECO-100 thru ECO-101: zinc diecast
- ECO-102 thru ECO-109: aluminum/natural

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1



ECO-100



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		No. Holes	Size Holes
		A	B		
1/2	ECO-100	2.70/68.6	3.25/82.6	4	19/64
3/4	ECO-101	2.80/71.1	3.64/92.5	2	3/8
				3	13/32
1	ECO-102	3.40/86.4	4.15/105.4	2	7/16
				3	1/2
1-1/4	ECO-103	3.32/84.3	4.61/117.1	2	27/64
				3	5/8
1-1/2	ECO-104	4.75/120.7	5.79/147.1	2	19/32
				1	7/16
2	ECO-105	5.75/146.1	6.90/175.3	3	3/4
				1	1
2-1/2	ECO-106	7.00/177.8	10.50/266.7	3	1-5/16
				1	7/8
3	ECO-107	8.50/215.9	11.75/298.5	3	1
				4	1-3/4
3-1/2	ECO-108	8.50/215.9	12.25/311.2	4	1-1/8
				3	1-3/4
4	ECO-109	8.75/222.3	12.50/317.5	4	1-1/8
				3	1-3/4

# NEER Aluminum Entrance Caps

## ECS: Set Screw Aluminum Entrance Caps

### Applications

- Set screw type aluminum entrance caps for unthreaded rigid conduit or IMC service masts.


### Standard Material/Finish

- Aluminum/natural

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1

COMMERCIAL PRODUCTS: SERVICE ENTRANCE FITTINGS



ECS-105

Trade Size (Inches)	Catalog Number	Dimensions in Inches/ Millimeters		No. Holes	Size Holes
		A	B		
2	ECS-105	5.50/139.7	7.00/177.8	2	3/4
				3	1
				1	1-5/16
2-1/2	ECS-106	7.25/184.2	10.25/260.4	3	7/8
				1	1
3	ECS-107	8.75/222.3	10.75/273.1	4	1-1/8
				3	1-3/4
3-1/2	ECS-108	9.25/235.0	13.50/342.9	4	1-1/8
				3	1-3/4
4	ECS-109	9.25/235.0	13.50/342.9	4	1/8
				3	3/4

Commercial Products

# NEER Aluminum Entrance Caps

## ECO: Clamp-on Aluminum Entrance Caps

### Applications


- Clamp type aluminum entrance caps for threaded or unthreaded rigid conduit, IMC or EMT service masts.

### Standard Material/Finish

- ECO-100 thru ECO-101: zinc diecast
- ECO-102 thru ECO-109: aluminum/natural

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1



ECO-100

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		No. Holes	Size Holes
		A	B		
1/2	ECO-100	2.70/68.6	3.25/82.6	4	19/64
3/4	ECO-101	2.80/71.1	3.64/92.5	2	3/8
				3	13/32
1	ECO-102	3.40/86.4	4.15/105.4	2	7/16
				3	1/2
1-1/4	ECO-103	3.32/84.3	4.61/117.1	2	27/64
				3	5/8
1-1/2	ECO-104	4.75/120.7	5.79/147.1	2	19/32
				1	7/16
2	ECO-105	5.75/146.1	6.90/175.3	3	3/4
				1	1
2-1/2	ECO-106	7.00/177.8	10.50/266.7	3	1-5/16
				1	7/8
3	ECO-107	8.50/215.9	11.75/298.5	3	1
				4	1-3/4
3-1/2	ECO-108	8.50/215.9	12.25/311.2	4	1-1/8
				3	1-3/4
4	ECO-109	8.75/222.3	12.50/317.5	4	1-1/8
				3	1-3/4

# NEER Aluminum Entrance Caps

## ECS: Set Screw Aluminum Entrance Caps

### Applications

- Set screw type aluminum entrance caps for unthreaded rigid conduit or IMC service masts.


### Standard Material/Finish

- Aluminum/natural

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1

COMMERCIAL PRODUCTS: SERVICE ENTRANCE FITTINGS



ECS-105

Trade Size (Inches)	Catalog Number	Dimensions in Inches/ Millimeters		No. Holes	Size Holes
		A	B		
2	ECS-105	5.50/139.7	7.00/177.8	2	3/4
				3	1
				1	1-5/16
2-1/2	ECS-106	7.25/184.2	10.25/260.4	3	7/8
				1	1
3	ECS-107	8.75/222.3	10.75/273.1	3	1-5/16
				4	1-1/8
3-1/2	ECS-108	9.25/235.0	13.50/342.9	3	1-3/4
				4	1-1/8
4	ECS-109	9.25/235.0	13.50/342.9	3	1/8
				3	3/4

Commercial Products