



Powering Business Worldwide

pe.eaton.com

Freedom Industrial Pump Panel

ECN5432AAG-R63/E

UPC:786685455327

Dimensions:

- **Height:** 12 IN
- **Length:** 40 IN
- **Width:** 20 IN

Weight:75 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V/60 Hz, 110V/50 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Disconnect:** Fusible
- **Frame Size:** NEMA size 3
- **Fuse Clip Rating:** 100A/600V
- **Fuse Clip Type:** Type R
- **Overload Relay:** 20-100A solid-state overload relay

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN5432AAG-R63/E](#)

Certifications:

- cUL Listed
- OSHPD Certified
- ABS Certified
- UL Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Freedom Industrial Pump Panel

ECN5432AAG-R63/E

UPC:786685455327

Dimensions:

- **Height:** 12 IN
- **Length:** 40 IN
- **Width:** 20 IN

Weight:75 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V/60 Hz, 110V/50 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Disconnect:** Fusible
- **Frame Size:** NEMA size 3
- **Fuse Clip Rating:** 100A/600V
- **Fuse Clip Type:** Type R
- **Overload Relay:** 20-100A solid-state overload relay

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN5432AAG-R63/E](#)

Certifications:

- cUL Listed
- OSHPD Certified
- ABS Certified
- UL Listed

Product compliance: No Data



