Specifications




Photo is representative

Eaton ECP183608

Eaton Crouse-Hinds series ECP enclosure, Square cover, 9-11/32" depth, 18" x 36" x 8", Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP183608
UPC	662276322004
PRODUCT LENGTH/DEPTH	23.66 in
PRODUCT HEIGHT	41.66 in
PRODUCT WIDTH	12.61 in
PRODUCT WEIGHT	355 lb

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 3R 4 7 9

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP183608 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	ECP Explosionproof Enclosures UL certification IECEx Certificate of Conformity Intertek EC-Type Examination Certificate
INSTALLATION INSTRUCTIONS	IF 1639 - ECP Explosionproof Enclosures IF 1107 - Mounting Plate Kit
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - ECP183608 ECP Enclosures

Product specifications

ENCLOSURE SIZE	18" x 36" x 8"
COVER TYPE	Square
DEPTH	9-11/32 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Specifications




Photo is representative

Eaton ECP183608

Eaton Crouse-Hinds series ECP enclosure, Square cover, 9-11/32" depth, 18" x 36" x 8", Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP183608
UPC	662276322004
PRODUCT LENGTH/DEPTH	23.66 in
PRODUCT HEIGHT	41.66 in
PRODUCT WIDTH	12.61 in
PRODUCT WEIGHT	355 lb

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 3R 4 7 9

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP183608 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	ECP Explosionproof Enclosures UL certification IECEx Certificate of Conformity Intertek EC-Type Examination Certificate
INSTALLATION INSTRUCTIONS	IF 1639 - ECP Explosionproof Enclosures IF 1107 - Mounting Plate Kit
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - ECP183608 ECP Enclosures

Product specifications

ENCLOSURE SIZE	18" x 36" x 8"
COVER TYPE	Square
DEPTH	9-11/32 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.