



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ELL112G Ocal 1-1/2"X90 Gray PVC CTD Elbow STL

Abb Installation Products, Inc

Catalog Number	ELL112G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 90 Degrees, Radius 8-1/4 Inch/209.55 Millimeters, Offset 11 Inch/279.40 Millimeters, Straight End 2-3/4 Inch/69.85 Millimeters, Unbent Length 18.46 Inch/468.86 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	4.6 (lbs/each)
Product Category	Steel

Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

Dimensions and Weight

Depth	18.46
-------	-------

Descriptions

Description	OCAL 1-1/2"X90 GRAY PVC CTD ELBOW STL
extra long description	ABB ELL11/2-G PVC CTD ELBOW 90D 1-1
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 90 Degrees, Radius 8-1/4 Inch/209.55 Millimeters, Offset 11 Inch/279.40 Millimeters, Straight End 2-3/4 Inch/69.85 Millimeters, Unbent Length 18.46 Inch/468.86 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 1-1/2IN STL Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

Manufacturer Information

Brand	OCAL
GTIN	00704508369927
Manufacturers Part Number	ELL11/2-G
UPC	704508369927

Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	Conduit Elbow - Standard Radius

Trade Size

Trade Size	1-1/2 in , 41 mm
------------	------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	8
Weight Per each	4.63

Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA