



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ELL2G Ocal 2"X90 Gray PVC CTD Elbow STL

*Abb Installation Products, Inc*

Catalog Number	ELL2G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 90 Degrees, Radius 9-1/2 Inch/241.30 Millimeters, Offset 13 Inch/330.20 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 21.92 Inch/556.83 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	6.9 (lbs/each)
Product Category	Steel

### Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

### Dimensions and Weight

Depth	21.92
-------	-------

### Descriptions

Description	OCAL 2"X90 GRAY PVC CTD ELBOW STL
extra long description	ABB ELL2-G PVC CTD ELBOW 90D 2IN ST
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 90 Degrees, Radius 9-1/2 Inch/241.30 Millimeters, Offset 13 Inch/330.20 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 21.92 Inch/556.83 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 2IN Steel Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

### Manufacturer Information

Brand	OCAL
GTIN	00704508370190
Manufacturers Part Number	ELL2-G
UPC	704508370190

### Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	Conduit Elbow - Standard Radius

### Trade Size

Trade Size	2 in , 53 mm
------------	--------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	6
Weight Per each	6.9

## Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA