



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EM3589 3/4 HP 1075 RPM 3 SPD 115V Blower MTR Shaft 1/2"X4 *Precision Electric Motor*

Catalog Number	EM3589
Manufacturer	Precision Electric Motor
Description	60 Hertz Frequency Rating; Ul, Csa Approval; Direct Drive Fan and Blower Application; 115 Volt Ac 1-Phase Voltage Rating; Resilient Ring, Extended Stud Mounting; 18 Pound Weight; 3/4 HP Power Rating; 1075 RPM Speed Rating; Oao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 10.2/7.3/4.5 Amp Motor Fla; Yes Reversible; 3 Speed(S); 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Flat; Orientation Horizontal; Bearing Type Ba
Weight per unit	19.0 (lbs/each)
Product Category	20190723150451

### Descriptions

Description	3/4 HP 1075 RPM 3 SPD 115V BLOWER MTR SHAFT 1/2"X4
Long Description	60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; DIRECT DRIVE FAN AND BLOWER APPLICATION; 115 VOLT AC 1-PHASE VOLTAGE RATING; RESILIENT RING, EXTENDED STUD MOUNTING; 18 POUND WEIGHT; 3/4 HP POWER RATING; 1075 RPM SPEED RATING; OAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 10.2/7.3/4.5 AMP MOTOR FLA; YES REVERSIBLE; 3 SPEED(S); 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE FLAT; ORIENTATION HORIZONTAL; BEARING TYPE BA
Product Type	Capacitor Start Motor

### Manufacturer Information

Brand	
GTIN	00786674019523
Manufacturers Part Number	D6066
UPC	786674019523

### Taxonomies, Classifications, and Categories

Category Description	Generic HAVCR Motors
----------------------	----------------------

### Packaging

Carton	1
Weight Per each	19