



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3731 3/4 HP 1075 RPM 208/230V Ball Bearing Shaft 1/2"X6

Precision Electric Motor

| | |
|------------------|--|
| Catalog Number | EM3731 |
| Manufacturer | Precision Electric Motor |
| Description | 60 Hertz Frequency Rating; UI, Csa Approval; Condenser Fan Application; 208 to 230 Volt Ac 1-Phase Voltage Rating; Extended Stud Mounting; 18 Pound Weight; 3/4 HP Power Rating; 1075 RPM Speed Rating; Teao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 4.6 to 5.3 Amp Motor Fla; Yes Reversible; 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Double Flat; Bearing Type Ball (Drive End); Number Of Poles 6; Overall Dimension |
| Weight per unit | 18.0 (lbs/each) |
| Product Category | 20190723150330 |

Descriptions

| | |
|------------------|--|
| Description | 3/4 HP 1075 RPM 208/230V BALL BEARING SHAFT 1/2"X6 |
| Long Description | 60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; CONDENSER FAN APPLICATION; 208 TO 230 VOLT AC 1-PHASE VOLTAGE RATING; EXTENDED STUD MOUNTING; 18 POUND WEIGHT; 3/4 HP POWER RATING; 1075 RPM SPEED RATING; TEAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 4.6 TO 5.3 AMP MOTOR FLA; YES REVERSIBLE; 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE DOUBLE FLAT; BEARING TYPE BALL (DRIVE END); NUMBER OF POLES 6; OVERALL DIMENSION |
| Product Type | Oem Motor |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | |
| GTIN | 00786674019585 |
| Manufacturers Part Number | 3S018 |
| UPC | 786674019585 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Generic HAVCR Motors |
|----------------------|----------------------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 18 |