

May 1, 2000  
Supersedes all previous



**E.M.T. Standard and Special Radius Elbows\***

**Galvanized E.M.T. 90°-45° Elbows**

NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 60° elbows deduct 10%, for 45° elbows deduct 15% and for 30° elbows deduct 20%.

Size	List Price per 100 Pieces	90°	45°	60°	30°	Carton Quantity	Approx. Weight per 100 Pieces (lbs)
½"	198.84	02021▲	02031■	02041■	02051■	50	28
¾"	200.13	02022▲	02032■	02042■	02052■	50	46
1"	261.47	02023▲	02033▲	02043■	02053■	25	86
1½"	378.10	02024▲	02034▲	02044■	02054■	25	148
1½"	493.17	02025▲	02035▲	02045■	02055■	20	198
2"	752.53	02026▲	02036▲	02046■	02056■	10	286
2½"	1832.22	02027▲	02037▲	02047■	02057■	Bulk	536
3"	2731.81	02028▲	02038▲	02048■	02058■	Bulk	720
3½"	3661.51	02029▲	02039■	02049■	02059■	Bulk	1080
4"	4307.69	02030▲	02040▲	02050■	02060■	Bulk	1333

PREFIX: EMTELB (SIZE) (DEGREE)

**E.M.T. Special Radius Elbows\***

All E.M.T. Special Radius Elbows are **NON-CANCELABLE** and **NON-RETURNABLE**

Size	List Price Each	15" Radius				App. Wt. (lbs.)	Size	List Price Each	18" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"						1½"							
1½"	31.55	02206●	●			4	1½"	33.99	02131●	●	●	●	4
2"							2"	40.09	02132●	●	●	●	6
2½"	52.60	02207●	●				2½"	61.21	02133●	●	●	●	

Size	List Price Each	24" Radius				App. Wt. (lbs.)	Size	List Price Each	30" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"	34.06	02092●	●	●	●	5	1½"						
1½"	44.83	02093●	●	●	●	5	1½"						
2"	49.13	02094●	02209●	●	●	7	2"	57.74	02102●	02210●	●	●	8
2½"	72.74	02095●	02095●	●	●	11	2½"						
3"	86.73	02096●	●	●	●	13	3"	102.03	02104●	●	●	●	14
3½"	127.15	02097●	●	●	●		3½"	158.95	02105●	●	●	●	19
4"	135.10	02098●	●	●	●	17	4"	152.75	02106●	●	●	●	21

Size	List Price Each	36" Radius				App. Wt. (lbs.)	Size	List Price Each	42" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"							1½"						
1½"	55.64	02109●	●	●	●	7	1½"						
2"	66.42	02110▲	●	●	●	9	2"						
2½"	90.93	02111■	●	●	●	13	2½"						
3"	119.73	02112●	●	●	●	16	3"						
3½"	166.09	02113●	●	●	●	22	3½"						
4"	166.74	02114▲	02212●	●	●	24	4"	203.87	02122●	02213●	●	●	28

Size	List Price Each	48" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°	
1½"						
1½"	68.80	23222●	●	●	●	9
2"	83.43	02126●	●	●	●	12
2½"						
3"	150.21	02128●	●	●	●	21
3½"	209.20	02129●	●	●	●	28
4"	232.49	02130▲	02214●	●	●	31

PREFIX: EMTELB (SIZE)(DEGREE)(RADIUS)

**Availability Codes**

Stock = ▲  
5 Days = ■  
10 Days = ●

\*UL Listed & Labeled  
Reference page 14 for approximate dimensions.

\*Note: All EMT can be made to the same dimensions as Rigid - Call the factory

Products on this page without UPC codes are currently being assigned UPC identification by NEMA. Information was not available at this time for printing.



# ECN KORN'S

## ROBROY INDUSTRIES

---

### ELBOWS

- Galvanized
- EMT
- IMC
- Aluminum

### COUPLINGS

- Galvanized
- Aluminum

### CLAMPS

The Original  
**"KORN'S CLAMP"**

- Right Angle (RA)  
Conduit Supports
- Edge Type (ET)  
Conduit Supports
- J-Clamps
- One Hole Straps
- Clampback Spacers
- U-Bolts
- SS Hardware
- Parallels (PAR)
- Beam Clamps

### NIPPLES

- Galvanized
- Aluminum

**MANUFACTURERS UPC #784011**

Price List  
Catalog F-162

Effective May 1, 2000  
Supercedes all previous

Revised: 3-22-2001

Dimensional and Material Specifications where applicable:  
Underwriters' Laboratories No. 6 A.N.S.I. C80.1, Fed. Specs. WW-C-581e

May 1, 2000  
Supersedes all previous



**E.M.T. Standard and Special Radius Elbows\***

**Galvanized E.M.T. 90°-45° Elbows**

NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 60° elbows deduct 10%, for 45° elbows deduct 15% and for 30° elbows deduct 20%.

Size	List Price per 100 Pieces	90°	45°	60°	30°	Carton Quantity	Approx. Weight per 100 Pieces (lbs)
½"	198.84	02021▲	02031■	02041■	02051■	50	28
¾"	200.13	02022▲	02032■	02042■	02052■	50	46
1"	261.47	02023▲	02033▲	02043■	02053■	25	86
1½"	378.10	02024▲	02034▲	02044■	02054■	25	148
1½"	493.17	02025▲	02035▲	02045■	02055■	20	198
2"	752.53	02026▲	02036▲	02046■	02056■	10	286
2½"	1832.22	02027▲	02037▲	02047■	02057■	Bulk	536
3"	2731.81	02028▲	02038▲	02048■	02058■	Bulk	720
3½"	3661.51	02029▲	02039■	02049■	02059■	Bulk	1080
4"	4307.69	02030▲	02040▲	02050■	02060■	Bulk	1333

PREFIX: EMTELB (SIZE) (DEGREE)

**E.M.T. Special Radius Elbows\***

All E.M.T. Special Radius Elbows are **NON-CANCELABLE** and **NON-RETURNABLE**

Size	List Price Each	15" Radius				App. Wt. (lbs.)	Size	List Price Each	18" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"	31.55	02206●	●			4	1½"	33.99	02131●	●	●	●	4
2"	52.60	02207●	●				2"	40.09	02132●	●	●	●	6
2½"							2½"	61.21	02133●	●	●	●	
							3"						
							3½"	96.58	02134●	●	●	●	
Size	List Price Each	24" Radius				App. Wt. (lbs.)	Size	List Price Each	30" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"	34.06	02092●	●	●	●	5	1½"						
1½"	44.83	02093●	●	●	●	5	1½"						
2"	49.13	02094●	02209●	●	●	7	2"	57.74	02102●	02210●	●	●	8
2½"	72.74	02095●	02095●	●	●	11	2½"						
3"	86.73	02096●	●	●	●	13	3"	102.03	02104●	●	●	●	14
3½"	127.15	02097●	●	●	●		3½"	158.95	02105●	●	●	●	19
4"	135.10	02098●	●	●	●	17	4"	152.75	02106●	●	●	●	21
Size	List Price Each	36" Radius				App. Wt. (lbs.)	Size	List Price Each	42" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"							1½"						
1½"	55.64	02109●	●	●	●	7	1½"						
2"	66.42	02110▲	●	●	●	9	2"						
2½"	90.93	02111■	●	●	●	13	2½"						
3"	119.73	02112●	●	●	●	16	3"						
3½"	166.09	02113●	●	●	●	22	3½"						
4"	166.74	02114▲	02212●	●	●	24	4"	203.87	02122●	02213●	●	●	28
Size	List Price Each	48" Radius				App. Wt. (lbs.)	Availability Codes						
		90°	45°	60°	30°		Stock = ▲	5 Days = ■	10 Days = ●				
1½"													
1½"	68.80	23222●	●	●	●	9							
2"	83.43	02126●	●	●	●	12							
2½"													
3"	150.21	02128●	●	●	●	21							
3½"	209.20	02129●	●	●	●	28							
4"	232.49	02130▲	02214●	●	●	31							

PREFIX: EMTELB (SIZE)(DEGREE)(RADIUS)

\*UL Listed & Labeled  
Reference page 14 for approximate dimensions.

\*Note: All EMT can be made to the same dimensions as Rigid - Call the factory

Products on this page without UPC codes are currently being assigned UPC identification by NEMA. Information was not available at this time for printing.



# ECN KORN'S

## ROBROY INDUSTRIES

---

### ELBOWS

- Galvanized
- EMT
- IMC
- Aluminum

### COUPLINGS

- Galvanized
- Aluminum

### CLAMPS

The Original  
"KORN'S CLAMP"

- Right Angle (RA)  
Conduit Supports
- Edge Type (ET)  
Conduit Supports
- J-Clamps
- One Hole Straps
- Clampback Spacers
- U-Bolts
- SS Hardware
- Parallels (PAR)
- Beam Clamps

### NIPPLES

- Galvanized
- Aluminum

**MANUFACTURERS UPC #784011**

Price List  
Catalog F-162

Effective May 1, 2000  
Supercedes all previous

Revised: 3-22-2001

Dimensional and Material Specifications where applicable:  
Underwriters' Laboratories No. 6 A.N.S.I. C80.1, Fed. Specs. WW-C-581e