On-Q

14-inch Enclosure with Screw-On Cover

Part No. EN1400



MADE IN USA

This 14"" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes

Features & Benefits

- 14-in Enclosure with Screw-On Cover
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Made in the USA
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Cover included

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023012	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Cable Entry	(6) rear knockouts
Frame	Cold Rolled Steel		

On-Q

14-inch Enclosure with Screw-On Cover

Part No. EN1400



MADE IN USA

This 14"" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes

Features & Benefits

- 14-in Enclosure with Screw-On Cover
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Made in the USA
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Cover included

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023012	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Cable Entry	(6) rear knockouts
Frame	Cold Rolled Steel		