


## Inner Panels *EP Series*

### Eclipse Series Enclosures



### Features

- Larger than standard NEMA panel used in same sized enclosure.
- 12 gauge steel construction.
- Larger sizes have 2 or 4 formed flanges for added strength.
- Slotted corner design for easier mounting.
- Finished in white or unpainted galvanized.



Mild Steel		Galvanized		Size		Gauge
Part No.	Part No.	D	E	D	E	
EP1210	EPG1210	10.20	8.20	10.20	8.20	12
EP1212	EPG1212	10.20	10.20	10.20	10.20	12
EP1224	EPG1224	10.20	22.20	10.20	22.20	12
EP1612	EPG1612	14.20	10.20	14.20	10.20	12
EP1616	EPG1616	14.20	14.20	14.20	14.20	12
EP1620	EPG1620	14.20	18.20	14.20	18.20	12
EP2012	EPG2012	18.20	10.20	18.20	10.20	12
EP2016	EPG2016	18.20	14.20	18.20	14.20	12
EP2020	EPG2020	18.20	18.20	18.20	18.20	12
EP2024	EPG2024	18.20	22.20	18.20	22.20	12
EP2412	EPG2412	22.20	10.20	22.20	10.20	12
EP2416	EPG2416	22.20	14.20	22.20	14.20	12
EP2420	EPG2420	22.20	18.20	22.20	18.20	12
EP2424	EPG2424	22.20	22.20	22.20	22.20	12
EP2430	EPG2430	22.20	28.20	22.20	28.20	12
EP2442	EPG2442	22.20	40.20	22.20	40.20	12
EP2448	EPG2448	22.20	46.20	22.20	46.20	12
EP3012	EPG3012	28.20	10.20	28.20	10.20	12
EP3016	EPG3016	28.20	14.20	28.20	14.20	12
EP3020	EPG3020	28.20	18.20	28.20	18.20	12
EP3024	EPG3024	28.20	22.20	28.20	22.20	12

<b>Mild Steel</b>		<b>Galvanized</b>		<b>Size</b>		<b>Gauge</b>
<b>Part No.</b>	<b>Part No.</b>	<b>D</b>	<b>E</b>			
<b>EP3030</b>	<b>EPG3030</b>	28.20	28.20			12
<b>EP3036</b>	<b>EPG3036</b>	28.20	34.20			12
<b>EP3042</b>	<b>EPG3042</b>	28.20	40.20			12
<b>EP3048</b>	<b>EPG3048</b>	28.20	46.20			12
<b>EP3060</b>	<b>EPG3060</b>	28.20	58.20			12
<b>EP3624</b>	<b>EPG3624</b>	34.20	22.20			12
<b>EP3630</b>	<b>EPG3630</b>	34.20	28.20			12
<b>EP3636</b>	<b>EPG3636</b>	34.20	34.20			12
<b>EP3642</b>	<b>EPG3642</b>	34.20	40.20			12
<b>EP3648</b>	<b>EPG3648</b>	34.20	46.20			12
<b>EP3660</b>	<b>EPG3660</b>	34.20	58.20			12
<b>EP4224</b>	<b>EPG4224</b>	40.20	22.20			12
<b>EP4230</b>	<b>EPG4230</b>	40.20	28.20			12
<b>EP4236</b>	<b>EPG4236</b>	40.20	34.20			12
<b>EP4824</b>	<b>EPG4824</b>	46.20	22.20			12
<b>EP4830</b>	<b>EPG4830</b>	46.20	28.20			12
<b>EP4836</b>	<b>EPG4836</b>	46.20	34.20			12
<b>EP4848</b>	<b>EPG4848</b>	46.20	46.20			12
<b>EP6036</b>	<b>EPG6036</b>	58.20	34.20			12
<b>EP7230</b>	<b>EPG7230</b>	70.20	28.20			12
<b>EP7236</b>	<b>EPG7236</b>	70.20	34.20			12

*Data subject to change without notice*


## Inner Panels *EP Series*

### Eclipse Series Enclosures



### Features

- Larger than standard NEMA panel used in same sized enclosure.
- 12gauge steel construction.
- Larger sizes have 2 or 4 formed flanges for added strength.
- Slotted corner design for easier mounting.
- Finished in white or unpainted galvanized.



Mild Steel		Galvanized		Size		Gauge
Part No.	Part No.	D	E	D	E	
EP1210	EPG1210	10.20	8.20	10.20	8.20	12
EP1212	EPG1212	10.20	10.20	10.20	10.20	12
EP1224	EPG1224	10.20	22.20	10.20	22.20	12
EP1612	EPG1612	14.20	10.20	14.20	10.20	12
EP1616	EPG1616	14.20	14.20	14.20	14.20	12
EP1620	EPG1620	14.20	18.20	14.20	18.20	12
EP2012	EPG2012	18.20	10.20	18.20	10.20	12
EP2016	EPG2016	18.20	14.20	18.20	14.20	12
EP2020	EPG2020	18.20	18.20	18.20	18.20	12
EP2024	EPG2024	18.20	22.20	18.20	22.20	12
EP2412	EPG2412	22.20	10.20	22.20	10.20	12
EP2416	EPG2416	22.20	14.20	22.20	14.20	12
EP2420	EPG2420	22.20	18.20	22.20	18.20	12
EP2424	EPG2424	22.20	22.20	22.20	22.20	12
EP2430	EPG2430	22.20	28.20	22.20	28.20	12
EP2442	EPG2442	22.20	40.20	22.20	40.20	12
EP2448	EPG2448	22.20	46.20	22.20	46.20	12
EP3012	EPG3012	28.20	10.20	28.20	10.20	12
EP3016	EPG3016	28.20	14.20	28.20	14.20	12
EP3020	EPG3020	28.20	18.20	28.20	18.20	12
EP3024	EPG3024	28.20	22.20	28.20	22.20	12

<b>Mild Steel</b>		<b>Galvanized</b>		<b>Size</b>	
<b>Part No.</b>	<b>Part No.</b>	<b>D</b>	<b>E</b>	<b>Gauge</b>	
<b>EP3030</b>	<b>EPG3030</b>	28.20	28.20	12	
<b>EP3036</b>	<b>EPG3036</b>	28.20	34.20	12	
<b>EP3042</b>	<b>EPG3042</b>	28.20	40.20	12	
<b>EP3048</b>	<b>EPG3048</b>	28.20	46.20	12	
<b>EP3060</b>	<b>EPG3060</b>	28.20	58.20	12	
<b>EP3624</b>	<b>EPG3624</b>	34.20	22.20	12	
<b>EP3630</b>	<b>EPG3630</b>	34.20	28.20	12	
<b>EP3636</b>	<b>EPG3636</b>	34.20	34.20	12	
<b>EP3642</b>	<b>EPG3642</b>	34.20	40.20	12	
<b>EP3648</b>	<b>EPG3648</b>	34.20	46.20	12	
<b>EP3660</b>	<b>EPG3660</b>	34.20	58.20	12	
<b>EP4224</b>	<b>EPG4224</b>	40.20	22.20	12	
<b>EP4230</b>	<b>EPG4230</b>	40.20	28.20	12	
<b>EP4236</b>	<b>EPG4236</b>	40.20	34.20	12	
<b>EP4824</b>	<b>EPG4824</b>	46.20	22.20	12	
<b>EP4830</b>	<b>EPG4830</b>	46.20	28.20	12	
<b>EP4836</b>	<b>EPG4836</b>	46.20	34.20	12	
<b>EP4848</b>	<b>EPG4848</b>	46.20	46.20	12	
<b>EP6036</b>	<b>EPG6036</b>	58.20	34.20	12	
<b>EP7230</b>	<b>EPG7230</b>	70.20	28.20	12	
<b>EP7236</b>	<b>EPG7236</b>	70.20	34.20	12	

*Data subject to change without notice*