ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESGS40 #2-4/0 Awg In-Line Gel Splice Kit (W/Connector)

Nsi Industries

Catalog Number	ESGS40
Manufacturer	Nsi Industries
Description	Splice Kit, Copper/Aluminum Conductor Material, Black Insulation Color, -40 °F Operating Temperature, +194 °F Operating Temperature, 4.229 In Overall Length, 1000 V, 0.26 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	2-4/0 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black

Descriptions

Description	#2-4/0 AWG IN-LINE GEL SPLICE KIT (W/CONNECTOR)
extra long description	NSI ESGS-4/0 In Line Gel Splice Kit
Special Features	Provides Sealed Splice For Underground, Buried, And Overhead Applications

Manufacturer Information

GTIN	00662381168610
UPC	662381168610

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	In-Line Gel Splice Kit

Packaging

Carton	3
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature	-40 C To 90 C
standard	ANSI C119.1-1986 Qualified