

### Key Features & Benefits:



- Rugged Die Cast Aluminum Housing:
  - Dark bronze polyester powder coat finish
- Optical Grade Polycarbonate Lens:
  - UV stabilized
  - Molded prismatic for optimal uniformity
  - Impact resistant
- Continuous Gasket for Weather-Tight Seal
- LEDs Mounted to and Protected by Aluminum Housing with Easy Driver Access Hinged Door
- (3) 3/4" Threaded knockouts:
  - (1) On back
  - (1) On either side
- Suitable for Wet Locations
- 10 Year Limited Warranty
- Mounting Options:
  - Direct to electrical box
  - Flush wall mount

Project: \_\_\_\_\_ Date: \_\_\_\_\_  
 Catalog #: \_\_\_\_\_  
 Notes: \_\_\_\_\_




### Technical Specifications:

Power: 30 Watts  
 Lumen Output: Up to 3,400 Lumens  
 Efficacy (lm/W): Up to 113 Lumens per Watt  
 Kelvin: 4000K, 5000K  
 CRI: >80  
 Input Voltage: 120-277 VAC  
 Life Span: 50,000 Hours  
 Operating Temperature: -40°F - 104°F  
 Dimensions (LxWxD): 14.21" x 9.25" x 7.4"



ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (lm/W)	KELVIN	DLC QPL CODE
ESL-WP-30W-240	30W	3,306	101	4000K	PWS4MG56
ESL-WP-30W-250	30W	3,400	113	5000K	PAFTZW91

### Ordering Guide:



### Options (Add as Suffix):

- ESL-WP-PC (Wall Pack Photocell for 30W-135W Wall Packs)
- ESL-4OCC (Occupancy Sensor, 0-10v Dimming, 8'-20' Mounting for 30W-135W Wall Packs)
- ESL-REM-101 (Remote control to self program 4OCC Sensor for 30W-135W Wall Packs)
- ESL-EMG-FDC-9.5W (Internal Emergency Backup 1,100 Lumens for the 30W Wall Pack, Factory Installed)
- ESL-EMG-AC-18W (External Emergency Backup 1,980 Lumens, Field Remote Mounted)

\* Other kelvin options available upon request

### Key Features & Benefits:



- Rugged Die Cast Aluminum Housing:
  - Dark bronze polyester powder coat finish
- Optical Grade Polycarbonate Lens:
  - UV stabilized
  - Molded prismatic for optimal uniformity
  - Impact resistant
- Continuous Gasket for Weather-Tight Seal
- LEDs Mounted to and Protected by Aluminum Housing with Easy Driver Access Hinged Door
- (3) 3/4" Threaded knockouts:
  - (1) On back
  - (1) On either side
- Suitable for Wet Locations
- 10 Year Limited Warranty
- Mounting Options:
  - Direct to electrical box
  - Flush wall mount

Project: \_\_\_\_\_ Date: \_\_\_\_\_  
 Catalog #: \_\_\_\_\_  
 Notes: \_\_\_\_\_




### Technical Specifications:

Power: 30 Watts  
 Lumen Output: Up to 3,400 Lumens  
 Efficacy (lm/W): Up to 113 Lumens per Watt  
 Kelvin: 4000K, 5000K  
 CRI: >80  
 Input Voltage: 120-277 VAC  
 Life Span: 50,000 Hours  
 Operating Temperature: -40°F - 104°F  
 Dimensions (LxWxD): 14.21" x 9.25" x 7.4"



ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (lm/W)	KELVIN	DLC QPL CODE
ESL-WP-30W-240	30W	3,306	101	4000K	PWS4MG56
ESL-WP-30W-250	30W	3,400	113	5000K	PAFTZW91

### Ordering Guide:



### Options (Add as Suffix):

- ESL-WP-PC (Wall Pack Photocell for 30W-135W Wall Packs)
- ESL-4OCC (Occupancy Sensor, 0-10v Dimming, 8'-20' Mounting for 30W-135W Wall Packs)
- ESL-REM-101 (Remote control to self program 4OCC Sensor for 30W-135W Wall Packs)
- ESL-EMG-FDC-9.5W (Internal Emergency Backup 1,100 Lumens for the 30W Wall Pack, Factory Installed)
- ESL-EMG-AC-18W (External Emergency Backup 1,980 Lumens, Field Remote Mounted)

\* Other kelvin options available upon request