



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1010RBQ 12-10AWG 1/5"STD Ylw Insltd Ring TRML *Panduit Corporation*

Catalog Number	EV1010RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-10RB-Q Contractor Grade Vinyl Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. Accommodates 12-10 Awg Wire Gauge, Compatible With #10 Stud, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	12-10AWG 1/5"STD YLW INSLTD RING TRML
extra long description	PAN EV10-10RB-Q StrongHold™ EV10-10
Long Description	StrongHold EV10-10RB-Q Contractor Grade Vinyl Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. Accommodates 12-10 AWG wire gauge, compatible with #10 Stud, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-10RB-Q Ring Terminal, Yellow, Vinyl, 1/5" S

Manufacturer Information

Brand	Panduit®
GTIN	00074983281855
Manufacturers Part Number	EV10-10RB-Q
UPC	074983281855



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Availability

minimum qty 25

Packaging

Carton 25

Package 250

Weight Per each 0.05

Uses, Certifications, and Standards

Mounting 0.31

standard CSA Certified LR31212;UL Listed 587H E52164