



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1014RBQ Stronghold™ EV10-14RB-Q R Panduit Corporation

Catalog Number	EV1014RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Ring Tongue Design Assures A Secure Connection In High Vibration Applications. Accommodates 12-10 Awg, Compatible With #1/4 Stud (M6), Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#10

Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

Dimensions and Weight

Size	1/4"
------	------

Descriptions

Description	STRONGHOLD™ EV10-14RB-Q R
extra long description	PAN EV10-14RB-Q StrongHold™ EV10-14
Long Description	StrongHold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The ring tongue design assures a secure connection in high vibration applications. Accommodates 12-10 AWG, compatible with #1/4 Stud (M6), are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-14RB-Q Ring Terminal, Yellow, Vinyl, 23/100

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983281862
Manufacturers Part Number	EV10-14RB-Q
UPC	074983281862



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Packaging

Carton 25

Package 250

Weight Per each 0.05

Uses, Certifications, and Standards

Mounting 0.31

standard UL Listed 587H E52164; CSA Certified LR31212