



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EV1014RBQ Stronghold™ EV10-14RB-Q R Panduit Corporation

Catalog Number	EV1014RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Ring Tongue Design Assures A Secure Connection In High Vibration Applications. Accommodates 12-10 Awg, Compatible With #1/4 Stud (M6), Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#10

### Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

### Dimensions and Weight

Size	1/4"
------	------

### Descriptions

Description	STRONGHOLD™ EV10-14RB-Q R
extra long description	PAN EV10-14RB-Q StrongHold™ EV10-14
Long Description	StrongHold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The ring tongue design assures a secure connection in high vibration applications. Accommodates 12-10 AWG, compatible with #1/4 Stud (M6), are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-14RB-Q Ring Terminal, Yellow, Vinyl, 23/100

### Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983281862
Manufacturers Part Number	EV10-14RB-Q
UPC	074983281862



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Packaging

Carton ..... 25

Package ..... 250

Weight Per each ..... 0.05

## Uses, Certifications, and Standards

Mounting ..... 0.31

standard ..... UL Listed 587H E52164; CSA Certified LR31212