



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **F017835ECO 17W T8 24" 3500K 82 Cri Bi-Pin** *Sylvania-Ledvance*

Catalog Number	F017835ECO
Manufacturer	Sylvania-Ledvance
Description	17W, 24" Mol, T8 Octron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.2400 (lbs/each)
Product Category	Linear Fluorescent Straight La

### **Features**

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	17

### **Material, Color, and Finish**

color rendering index (cri)	82
Finish	Phosphor Coated

### **Descriptions**

Description	17W T8 24" 3500K 82 CRI BI-PIN
extra long description	SYL FO17835ECO/22136 FO17835ECO 30/
Long Description	17W, 24" MOL, T8 OCTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 82 CRI, suitable for IS or RS operation, ECOLOGIC

### **Manufacturer Information**

Brand	SYLVANIA
GTIN	00046135221361
Manufacturers Part Number	FO17/835/ECO/22136
UPC	046135221361

### **Taxonomies, Classifications, and Categories**

Category Description	Fluorescent
Type	FLUORESCENT

### **Packaging**

Carton	1
Package	30
Weight Per each	0.24