



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F028841XPSSECO 28W T8 48" 4100K 85CRI Bi-Pin *Sylvania-Ledvance*

Catalog Number	F028841XPSSECO
Manufacturer	Sylvania-Ledvance
Description	28W, 48" Mol, T8 Octron Extended Performance Supersaver Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For RS or Is Operation, Ecologic 3
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	40000
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	28

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	28W T8 48" 4100K 85CRI BI-PIN
extra long description	SYL FO28841XPSSECO3/22179 FO28841XP
Long Description	28W, 48" MOL, T8 OCTRON Extended Performance Supersaver fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for RS or IS operation, ECOLOGIC 3
Product Type	F028841XPSSECO3 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221798
Manufacturers Part Number	FO28/841/XP/SS/ECO3/22179
UPC	046135221798

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------