



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F032841XPECO 32W T8 48" 4100K 85 Cri Bi-Pin Energy Saving

*Sylvania-Ledvance*

Catalog Number	F032841XPECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron XP Extended Performance Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Is or RS Operation, Ecologic 3
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

### Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

### Descriptions

Description	32W T8 48" 4100K 85 CRI BI-PIN ENERGY SAVING
extra long description	SYL FO32841XPECO3/21767 FO32841XPEC
Long Description	32W, 48" MOL, T8 OCTRON XP Extended Performance fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC 3

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135217678
Manufacturers Part Number	FO32/841/XP/ECO3/21767
UPC	046135217678

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	30
Weight Per each	0.45