



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032841XPECO 32W T8 48" 4100K 85 Cri Bi-Pin Energy Saving

Sylvania-Ledvance

Catalog Number	F032841XPECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron XP Extended Performance Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Is or RS Operation, Ecologic 3
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	32W T8 48" 4100K 85 CRI BI-PIN ENERGY SAVING
extra long description	SYL FO32841XPECO3/21767 FO32841XPEC
Long Description	32W, 48" MOL, T8 OCTRON XP Extended Performance fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC 3

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135217678
Manufacturers Part Number	FO32/841/XP/ECO3/21767
UPC	046135217678

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.45