



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032850ECO 32W T8 48" 5000K 82 Cri Bi-Pin Energy Saving *Sylvania-Ledvance*

Catalog Number	F032850ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron Fluorescent Lamp, 5000K Color Temperature, Rare Earth Phosphor, 81 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	81
color temperature	5000
Finish	Phosphor Coated

Descriptions

Description	32W T8 48" 5000K 82 CRI BI-PIN ENERGY SAVING
extra long description	SYL FO32850ECO/22143 FO32850ECO 30/
Long Description	32W, 48" MOL, T8 OCTRON fluorescent lamp, 5000K color temperature, rare earth phosphor, 81 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221439
Manufacturers Part Number	FO32/850/ECO/22143
UPC	046135221439

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.45