



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032865XPECO 32W T8 48" 6500K 85 Cri Bi-Pin Energy Saving

Sylvania-Ledvance

Catalog Number	F032865XPECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron XP Extended Performance Fluorescent Lamp, 6500K Color Temperature Rare Earth Phosphor, 80 Cri, Suitable For Is or RS Operation, Ecologic.
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	85
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	32W T8 48" 6500K 85 CRI BI-PIN ENERGY SAVING
extra long description	SYL FO32865XPECO/21720 FO32865XPECO
Long Description	32W, 48" MOL, T8 OCTRON XP Extended Performance fluorescent lamp, 6500k color temperature rare earth phosphor, 80 CRI, suitable for IS or RS operation, ECOLOGIC.

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135217203
Manufacturers Part Number	FO32/865/XP/ECO/21720
UPC	046135217203

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	30
Weight Per each	0.45



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial/Residential