



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032V41ECO 32W T8 48" 4100K 90 Cri *Sylvania-Ledvance*

Catalog Number	F032V41ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48 Inch Mol, T8 Octron Vivid Value Fluorescent Lamp Combines Vivid Color Rendering With Entry Level Value, 4100K Color Temperature, Rare Earth Phosphor, 90 Cri, Suitable For Is or PRS Operation, Ecologic . Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.4207 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bipin
Lamp Type	RAPID & INSTANT START
lumens	2450
Shape	T8

Material, Color, and Finish

color rendering index (cri)	90
-----------------------------	----

Descriptions

Description	32W T8 48" 4100K 90 CRI
extra long description	SYL FO32V41ECO/22438 FO32V41ECO 30/
Long Description	32W, 48 inch MOL, T8 OCTRON VIVID VALUE fluorescent lamp combines VIVID color rendering with entry level VALUE, 4100K color temperature, rare earth phosphor, 90 CRI, suitable for IS or PRS operation, ECOLOGIC . VIVID Color: High CRI lamps for color critical applications.

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135224386
Manufacturers Part Number	FO32/V41/ECO/22438
UPC	046135224386

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.4207